

LUXSER Illuseo™

NEW
GENERATION
PLATFORM
FOR NEXT
LEVEL RESULTS



- Unique Vacuum + RF +
- Microneedling Gold Plated &
- Insulation Needles Virtually No
- Downtime For All SkinTypes




LUXSER Illuseo™




UNIQUE VACUUM + RF + MICRONEEDLING
THE LUXSER ILLUSEO
ELEVATES THE STANDARD FOR SKIN

UNIQUE VACUUM + RF + MICRONEEDLING




UNIQUE VACUUM SUCTION TECHNOLOGY

Allows you to pull up the treatment area to stabilise the microneedles for safer and more precise treatments especially useful around the delicate eye area.



RF ENERGY

Penetrate deep into the dermis, promote collagen and elastin production, No Pain, No Downtime.



INSULATED MICRO NEEDLES

With ultra-fine needles and unique vacuum features, it delivers safe and effective Micro-needling treatments with reduced discomfort and downtime compared to other devices.

THREE TECHNOLOGY IN ONE

LUXSER Illuseo™



Pore Reduction



Acne Scarring



Improve Skin tone




Wrinkle Removal



Skin tightening



Stretch Marks



Vacuum technology is used to stabilise the microneedles for safer and more precise treatments, especially useful around the delicate eye area.

FASTER TREATMENTS THAT DELIVER CONSISTENT OUTCOMES AND PROVIDE PATIENT COMFORT

REPLACE

Ergonomic design, easy and simple operation, needles are easy to replace.

FASTER

Faster treatment, delivers consistent results and makes patients feel professional.


COMFORTABLE

Ultra-fine microneedle reduces bleeding and is more comfortable.




AVAILABLE IN MULTIPLE SIZES TO SUIT DIFFERENT PARTS

MRF MICRO-NEEDLES TIPS




3x3
9 PINS
For Eye Around And Nose Area



5x4
20 PINS
For Forehead Area



5x5
25 PINS
For Face Area



7x7
49 PINS
For Arms, Legs & Body



RF + VACUUM TIPS




5x6
For Fine Wrinkle Treatment




UNIQUE VACUUM SUCTION TECHNOLOGY

Pull up the treatment area to stabilise the Microneedles for safer and more precise treatment.



0.5-4mm

● Treating Depth 0.5-4mm Adjustable



Only The Needle Tips Deliver Power

- Targeted Treatment
- Minimized Discomfort
- Reduced Risk of Side Effects

